



Han® PushPull, type acc. to IEC 61076-3-118  
Housing bulkhead mounting and power females for device integration

## Features

- HARTING PushPull technology
- Compact, space-saving design
- Touch-proof
- Device side: male
  - Solder variant, angled and straight
- 4 times coding without contact loss

## Technical characteristics

|                                      |   |
|--------------------------------------|---|
| Locking                              | PushPull technology acc. to IEC 61076-3-118 |
| Degree of protection                 | IP65 / IP67                                 |
| Number of contacts                   | 4 + PE                                      |
| Electrical data acc. to DIN EN 61984 | 16 A 230/400 V 4 kV 3                       |
| Termination                          | Male insert with solder termination         |
| Mating cycles                        | min. 500                                    |
| Temperature range                    | -40 °C ... +70 °C                           |
| Housing material                     | Plastic, black                              |
| Flammability acc. to UL 94           | V0  |

| Identification                               | Part number    | Drawing | Dimensions in mm |
|--|----------------|---------|------------------|
| <b>Components device side</b>                |                |         |                  |
| Housing bulkhead mounting plastic            | 09 35 002 0323 |         |                  |
| Protection cover IP65 / IP67                 | 09 35 002 5402 |         |                  |
| Coding pins                                  | 09 35 000 6190 |         |                  |
| Male insert with solder termination angled   | 09 35 002 3003 |         |                  |
| Male insert with solder termination straight | 09 35 002 3004 |         |                  |