

Han® PushPull, type acc. to IEC 61 076-3-118 variant 14 Accessories

Identification	Part number	Drawing	Dimensions in mm
Crimping tool	09 99 000 0888		
Locator Han P® for crimping tool 09 99 000 0888	09 99 000 0886		
Removal tool Han P®	09 99 000 0319		
Coding pins for 4 times coding without contact loss	09 35 000 6190		

Identification	Part number		Drawing	Dimensions in mm																								
	Male contact	Female contact																										
Crimp contacts Han® P silver plated	for 0.5 mm ²	09 35 000 6103	09 35 000 6203	<table border="1"> <thead> <tr> <th colspan="2">Wire gauge</th> <th>Ø</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>for 0.5 mm²</td> <td>AWG 20</td> <td>1.15 mm</td> <td>6 mm</td> </tr> <tr> <td>for 0.75 mm²</td> <td>AWG 18</td> <td>1.30 mm</td> <td>6 mm</td> </tr> <tr> <td>for 1.0 mm²</td> <td>AWG 18</td> <td>1.45 mm</td> <td>6 mm</td> </tr> <tr> <td>for 1.5 mm²</td> <td>AWG 16</td> <td>1.75 mm</td> <td>6 mm</td> </tr> <tr> <td>for 2.5 mm²</td> <td>AWG 14</td> <td>2.25 mm</td> <td>6 mm</td> </tr> </tbody> </table>	Wire gauge		Ø	Stripping length	for 0.5 mm ²	AWG 20	1.15 mm	6 mm	for 0.75 mm ²	AWG 18	1.30 mm	6 mm	for 1.0 mm ²	AWG 18	1.45 mm	6 mm	for 1.5 mm ²	AWG 16	1.75 mm	6 mm	for 2.5 mm ²	AWG 14	2.25 mm	6 mm
	Wire gauge		Ø		Stripping length																							
	for 0.5 mm ²	AWG 20	1.15 mm		6 mm																							
	for 0.75 mm ²	AWG 18	1.30 mm		6 mm																							
	for 1.0 mm ²	AWG 18	1.45 mm		6 mm																							
	for 1.5 mm ²	AWG 16	1.75 mm		6 mm																							
for 2.5 mm ²	AWG 14	2.25 mm	6 mm																									
for 0.75 mm ²	09 35 000 6104	09 35 000 6204																										
for 1.0 mm ²	09 35 000 6105	09 35 000 6205																										
for 1.5 mm ²	09 35 000 6106	09 35 000 6206																										
for 2.5 mm ²	09 35 000 6107	09 35 000 6207																										