



## HARTING RJ Industrial® RJ45 – coupler and adapter PCB's

### Advantages

- Compatible with Han® 3 A<sup>1)</sup> and HARTING PushPull
- Suitable for PoE (IEEE 802.3af) and PoE+ (IEEE 802.3at)
- Temperature range -40 °C ... +70 °C

### Technical characteristics

Rated voltage	125 V AC
Rated current	1.5 A
Mating face	RJ45 acc. to IEC 60603-7
Mating cycles	min. 750

Identification	Part number	Drawing	Dimensions in mm
<b>Coupler PCB</b> 2x RJ45 8-poles  2 x RJ45 jack (09 45 551 1102)  1 x RJ45 jack horizontal (09 45 551 1102) and 1 x RJ45 jack vertical (09 45 551 1103)	09 45 545 1130  09 45 545 1138		
<b>Adapter PCB</b> 1x RJ45 8-poles  to solder points	09 45 545 1134		
<b>Adapter PCB</b> 1x RJ45 8-poles  cage clamp, 5-pole, 1.5 mm <sup>2</sup>	09 45 545 1135		

<sup>1)</sup> with suitable adapter, see page 04.04