

Number of contacts

9–50



Solder buckets

Identification	No. of contacts	Part number	
Performance levels Explanations see page 05.04 Other performance levels on request		Performance level 3	Performance level 2
Male connector metal shell with dimples		turned contacts 9 09 67 009 5604 15 09 67 015 5604 25 09 67 025 5604 37 09 67 037 5604 50 09 67 050 5604 stamped contacts 9 09 67 209 5604 15 09 67 215 5604 25 09 67 225 5604 37 09 67 237 5604 50 09 67 250 5604	turned contacts 9 09 67 009 5615 15 09 67 015 5615 25 09 67 025 5615 37 09 67 037 5615 50 09 67 050 5615 stamped contacts 9 09 67 209 5615 15 09 67 215 5615 25 09 67 225 5615 37 09 67 237 5615 50 09 67 250 5615
Female connector metal shell		turned contacts 9 09 67 009 4704 15 09 67 015 4704 25 09 67 025 4704 37 09 67 037 4704 50 09 67 050 4704 stamped contacts 9 09 67 209 4704 15 09 67 215 4704 25 09 67 225 4704 37 09 67 237 4704 50 09 67 250 4704	turned contacts 9 09 67 009 4715 15 09 67 015 4715 25 09 67 025 4715 37 09 67 037 4715 50 09 67 050 4715 stamped contacts 9 09 67 209 4715 15 09 67 215 4715 25 09 67 225 4715 37 09 67 237 4715 50 09 67 250 4715

D-Sub