

Number of contacts 6, 8, 10 ... 96, 98, 100

Rated voltage 150 V

Core structure AWG 30/7

Strain relief with / without

Connector direction same / different

Wiring 1 : 1 / crossed

Cable types

PVC


Operating temperatures -20 °C ... +105 °C

Halogen free


Operating temperatures -40 °C ... +125 °C

Options

Option 1



Option 2



Option 3

