



Identification	Part No.	Drawing	Dimensions in mm
<p>HARTING PushPull Outdoor cable, RJ45, 8-wire, Cat. 5e</p> <p>Length: a = 1.5 m a = 3.0 m a = 5.0 m a = 10.0 m a = 20.0 m</p>	<p>09 45 745 1105 09 45 745 1107 09 45 745 1109 09 45 745 1114 09 45 745 1116</p>	<p>double ended</p> <p>a = length</p>	
<p>Han® 3 A Outdoor cable, RJ45, 8-wire, Cat. 5e</p> <p>Length: a = 1.5 m a = 3.0 m a = 5.0 m a = 10.0 m a = 20.0 m</p>	<p>09 45 715 1105 09 45 715 1107 09 45 715 1109 09 45 715 1114 09 45 715 1116</p>	<p>double ended</p> <p>a = length</p>	
<p>Outdoor cable 8-wire, RJ45, Cat. 5 / Cat. 5e, PVC</p> <p>Length: 20 m ring Length: 50 m ring Length: 100 m ring Length: 500 m reel</p>	<p>09 45 600 0230 09 45 600 0240 09 45 600 0200 09 45 600 0220</p>	<p>Wire: bare stranded copper, AWG 26/7</p> <p>Overall screen: aluminium bonded polyester tape and tinned copper wire braid, braid coverage about 85 %</p> <p>Overall diameter: 6.5 – 6.9 mm</p>	

Further cable lengths are available on request