

Identification

Part No.

Drawing

Dimensions in mm


Han® M12 to RJ45 (IP20),
overmoulded
System cable, D-coding,
4-wire

AWG 22/7
trailing PUR


Length: a = 1.5 m
a = 3.0 m
a = 5.0 m
a = 10.0 m
a = 20.0 m

09 45 700 5023
09 45 700 5025
09 45 700 5027
09 45 700 5051
09 45 700 5053

double ended



a = length



Han® M12 to RJ45,
overmoulded
System cable, D-coding,
4-wire

AWG 22/7
stranded PVC outdoor

Length: a = 1.5 m
a = 3.0 m
a = 5.0 m
a = 10.0 m
a = 20.0 m

09 45 700 5064
09 45 700 5066
09 45 700 5068
09 45 700 5073
09 45 700 5075

Contact assignment

Signal	M12 D-coding	RJ45
TD+	1	1
TD-	3	2
RD+	2	3
RD-	4	6