



Ethernet Switch Ha-VIS eCon 9070-B

7-port Ethernet Switch for installation in a 19" rack

Unmanaged	IP20	PROFINET compatible <input checked="" type="checkbox"/>	EtherNet/IP compatible <input checked="" type="checkbox"/>
Number of ports, Copper / Termination	7x 10/100Base-T(X) / M12 D-coding		
Input voltage / Termination	24 / 48 V DC / M12 A-coding, male		
Permissible range (min./max.)	8 V ... 60 V DC		
Input current	approx. 150 mA (at 24 V DC)		
Housing material	aluminium, anodised		
Dimensions (W x H x D)	60.6 mm (3 U) x 128.4 mm (12 HP) x 167.5 mm		
Weight	approx. 0.6 kg		
Working temperature	-40 °C ... +70 °C		
MTBF	1.411.000 h		

Identification	Part number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

Ha-VIS eCon 9070-B
Ethernet Switch with
7 ports M12 D-coding

20 76 207 7000

