



Han® 3 A RJ45 System cable, 8-wire

RJ45 connector cable Han® 3 A for IP65 / IP67 applications to RJ45 (IP20)

RJ45 cords

PVC / PUR	<input checked="" type="checkbox"/>	8 wire	<input checked="" type="checkbox"/>	4 wire	<input type="checkbox"/>	Cat. 5e	<input type="checkbox"/>	Cat. 6	<input checked="" type="checkbox"/>	Cat. 6A	<input type="checkbox"/>	Cat. 7	<input type="checkbox"/>
-----------	-------------------------------------	--------	-------------------------------------	--------	--------------------------	---------	--------------------------	--------	-------------------------------------	---------	--------------------------	--------	--------------------------

Connector types	Han® 3 A RJ45 (IP65 / IP67) RJ45 (IP20)
Cable types	4 x 2, Twisted Pair, shielded
Sheath material	PVC / PUR
Wiring	8-pole, 1:1
Transmission performance	Category 6 / Class E up to 250 MHz acc. to ISO/IEC 11 801:2002, EN 50 173-1
Transmission rate	10/100/1000 Mbit/s
Shielding	Fully shielded, 360° shielding contact
Operating temperature range	-10 °C to +70 °C

Standard lengths	1.5 m / 3 m / 5 m / 10 m / 20 m other lengths available on request
Colour	Yellow

- Advantages**
- Very robust metal housing Han® 3 A for IP65 / IP67
 - Additional locking
 - Easy change-over from harsh industrial environment to protected IP20 environment
 - Easy handling for all applications

Identification	Part number		Drawing	Dimensions in mm
	PVC	PUR		
Han® 3 A RJ45 System cable, 8-wire IP65 / IP67 to IP20	Yellow	Yellow		
Length 1.5 m	09 45 701 1564	09 45 701 1534		
Length 3.0 m	09 45 701 1566	09 45 701 1536		
Length 5.0 m	09 45 701 1568	09 45 701 1538		
Length 10.0 m	09 45 701 1573	09 45 701 1543		
Length 20.0 m	09 45 701 1575	09 45 701 1545		