



har-port USB coupler

Advantages

- Compact and well-shaped service interface in a timeless attractive design
- Easy mounting
- Compact and robust design
- Practical accessories

Technical characteristics

Number of ports	2x USB Typ A
Mounting	Screwable in cover plates
Degree of protection	IP20
Mating cycles	min. 1500
Temperature range	-25 °C ... +70 °C
Housing material	Polyamide

Identification	Part No.	Drawing	Dimensions in mm
<i>har-port</i> USB 2.0 A-A coupler	09 45 452 1901		
<i>har-port</i> USB 3.0 A-A coupler	09 45 452 1902		
<i>har-port</i> USB 2.0 A-A coupler with cable	Length: 0.15 m 09 45 452 1927 0.4 m 09 45 452 1928 0.5 m 09 45 452 1920 1.0 m 09 45 452 1921 1.5 m 09 45 452 1922 2.0 m 09 45 452 1923 3.0 m 09 45 452 1924 4.0 m 09 45 452 1926 5.0 m 09 45 452 1925		
<i>har-port</i> USB 2.0 B-B coupler with cable	Length: 0.5 m 09 45 452 1910 1.0 m 09 45 452 1911 1.5 m 09 45 452 1912 2.0 m 09 45 452 1913 3.0 m 09 45 452 1914 4.0 m 09 45 452 1916 5.0 m 09 45 452 1915		