



Unmanaged Plug-and-Play Ethernet Switches

for Assembly on DIN Rail in Control Cabinets

Commercial Temp.: 0 °C ... +55 °C / Industrial Temp.: -40 °C ... +70 °C

Power Sourcing Equipment (PSE) with 4 Ports PoE+ (34.2 watts per port)

Specification

| | |
|--|---|
| Number of ports copper / termination including PoE+ ports | 7 x 10BASE-T _e / 100BASE-TX EEE / 1000BASE-T EEE RJ45 (twisted pair) 4 x PoE+ with 34.2 watts per port |
| Nominal voltage (without PoE / PoE / PoE+) Permissible voltage range Termination | 24 / 48 / 54 VDC ≡ 9 V ... 60 VDC ≡ Screw type terminal block, pluggable, 3-poles (+ / - / ≡) |
| Current consumption typical @ 24 V / 48 V / 54 V | 0.19 A / 1.48 A / 2.45 A |
| Dimensions (W x H x D) | 25.0 x 142.0 x 107.5 mm (without pluggable screw type terminal block) |
| Weight | 531 g |
| MTBF in million hours | 0.63 |
| Approvals | CE FCC CFR 47 Part 15, cUL US 508 listed, Det Norske Veritas (DNV), Germanischer Lloyd (GL), American Bureau of Shipping (ABS), Nippon Kaiji Kyokai (NK) |

| Identification | Part number | Drawing | Dimensions in mm |
|----------------|-------------|---------|------------------|
|----------------|-------------|---------|------------------|

| | |
|---|----------------|
| Ha-VIS eCon 3070GB-A-P 0 °C ... +55 °C | 24 03 407 0030 |
|---|----------------|

| | |
|--|----------------|
| Ha-VIS eCon 3070GBT-A-P -40 °C ... +70 °C | 24 03 407 0020 |
|--|----------------|

