


Number of contacts

max. 24




Interface connector I

Identification	No. of contacts	Part number	Drawing	Dimensions in mm
Interface connector I for male crimp contacts Order contacts separately	24	09 26 024 3411		

Identification	Identification Wire gauge	Part number	Performance levels according to IEC 60603-2. Explanation chapter 00
			2 1
Male crimp FC contacts			
Bandoliered contacts (approx. 2,500 pieces)	1	09 06 000 9564	09 06 000 9544
	2	09 06 000 9561	09 06 000 9541
	3	09 06 000 9562	09 06 000 9542
Bandoliered contacts (approx. 250 pieces)	2		09 06 000 5541
	3		09 06 000 5542
Individual contacts ¹⁾	1	09 06 000 9574	09 06 000 9554
	2	09 06 000 9571	09 06 000 9551
	3	09 06 000 9572	09 06 000 9552

FC 1 FC 2 FC 3	1 2 3	Wire gauge mm ² AWG	Insulation ø mm	Identification
		0.09 - 0.25 28 - 24	0.7 - 1.5	
		0.14 - 0.56 26 - 20	0.8 - 2.0	
		0.5 - 1.5 20 - 16	1.6 - 2.8	
		3.5 + 0.5 mm of insulation is stripped from the wires to be crimped		Bandoliered contacts
		For the fabrication in line with the specification please use exclusively crimp tools approved by HARTING (see DIN EN 60352-2)		Individual contacts
		Insertion, removal and crimping tools see chapter 30		



DIN Power up to 6 A

¹⁾ Packaging unit 1,000 pieces