


Open hood G, junction element O, locking lever



Identification	Part number	Drawing	Dimensions in mm
<p>Open hood G I</p> <p>for types E, F, H and MH, for applications A B C</p> <p>Supplied with:</p> <p>Open hood 1x</p> <p>Locking screw 2x (09 06 000 9958)</p> <p>Cable tie 1x</p> <p>Screw 2x</p>	09 06 000 9957	<p>2 x ST 2.2 x 9.5 F-Z; E1U; ISO 7049</p>	
<p>Open hood G II</p> <p>for types E, F, H and MH, for application C</p> <p>Supplied with:</p> <p>Open hood 1x</p> <p>Pre-assembled, undetachable locking screw 2x</p> <p>Cable tie 1x</p> <p>Screw 2x</p>	09 06 001 9939		
<p>Junction element O IV</p> <p>for type F</p> <p>Supplied with:</p> <p>Junction element 2x</p> <p>Cable tie 2x</p> <p>Screw 2x</p> <p>Screw M2.5 x 20 2x</p>	09 06 000 9968	<p>2 x ST 2.2 x 9.5 F-Z; E1U; ISO 7049</p>	
<p>Locking lever III</p> <p>for type F, H and MH</p> <p>Supplied with:</p> <p>Locking lever 2x</p>	<p>09 06 000 9930¹⁾</p> <p>09 06 000 9911¹⁾</p>		

Shell housings