
















Series	Han® 200 A Axial module	Han® 200 A Axial module	Han® 200 A PE Axial module	Han® 200 A PE Axial module
Number of contacts	1	1	1	1
Termination	Axial screw terminal 	Axial screw terminal 	Axial screw terminal 	Axial screw terminal 
Rated current	200 A	200 A	200 A	200 A
Rated voltage	1000 V	1000 V	1000 V	1000 V
Wire gauge	25 ... 40 mm ²	40 ... 70 mm ²	25 ... 40 mm ²	40 ... 70 mm ²
Male insert (M)	09 14 001 2663	09 14 001 2662	09 14 001 2668	09 14 001 2667
Female insert (F)	09 14 001 2763	09 14 001 2762	09 14 001 2768	09 14 001 2767

Series	Han® 200 A Crimp module	Han® 100 A Axial module	Han® 100 A Axial module	Han® 100 A Axial module
Number of contacts	1	2	2	2
Termination	Crimp terminal 	Axial screw terminal 	Axial screw terminal 	Axial screw terminal 
Rated current	200 A	100 A	100 A	100 A
Rated voltage	1000 V	1000 V	1000 V	1000 V
Wire gauge	25 ... 70 mm ²	10 ... 25 mm ²	16 ... 35 mm ²	38 mm ²
Male insert (M)	09 14 001 3001	09 14 002 2653	09 14 002 2651	09 14 002 2650
Female insert (F)	09 14 001 3101	09 14 002 2753	09 14 002 2751	09 14 002 2750

Series	Han® 100 A Crimp module	Han® 100 A Single module	Han® 70 A Axial module	Han® 70 A Axial module
Number of contacts	2	2	2	2
Termination	Crimp terminal 	Axial screw terminal + Crimp terminal 	Axial screw terminal 	Axial screw terminal 
Rated current	100 A	100 A	70 A	70 A
Rated voltage	1000 V	830 V	1000 V	1000 V
Wire gauge	10 ... 35 mm ²	10 ... 35 mm ²	6 ... 16 mm ²	14 ... 22 mm ²
Male insert (M)	09 14 002 3501	09 14 001 3031	09 14 002 2646	09 14 002 2647
Female insert (F)	09 14 002 3151	09 14 001 3131	09 14 002 2741	09 14 002 2742

Series	Han® 70 A Axial module	Han® 70 A Axial module	Han® 70 A Crimp module	Han® 70 A Hybrid module
Number of contacts	2	2	2	1 / 4
Termination	Axial screw terminal with finger protected male contacts 	Axial screw terminal with finger protected male contacts 	Crimp terminal 	Axial screw terminal 
Rated current	70 A	70 A	70 A	1 x 70 A / 4 x 16 A
Rated voltage	1000 V	1000 V	1000 V	1000 V / 400 V
Wire gauge	6 ... 16 mm ²	14 ... 22 mm ²	10 ... 25 mm ²	6 ... 16 mm ² / 0.14 ... 4 mm ²
Male insert (M)	09 14 002 2641	09 14 002 2642	09 14 002 3041	09 14 005 2646
Female insert (F)	09 14 002 2741	09 14 002 2742	09 14 002 3141	09 14 005 2741