

|                    |                   |                  |                |                 |                 |
|--------------------|-------------------|------------------|----------------|-----------------|-----------------|
| Series             | Han® Multi module |                  |                |                 |                 |
| Number of contacts | 12                |                  |                |                 |                 |
| Modules            |                   |                  |                |                 |                 |
| Male insert (M)    | 09 14 012 4501    |                  |                |                 |                 |
| Female insert (F)  | 09 14 012 4512    |                  |                |                 |                 |
| Contacts           | F.O. contact      | F.O. contact     | F.O. contact   | Coaxial contact | Coaxial contact |
|                    |                   |                  |                |                 |                 |
|                    | Multimode F.O.    | HCS®* / PCF F.O. | 1 mm POF       | 50 Ω RG 174     | 75 Ω RG 179     |
| Male contact       | 20 10 230 4211    | 20 10 125 4212   | 20 10 001 4211 | 09 14 000 6211  | 09 14 000 6221  |
| Female contact     | 20 10 230 4221    | 20 10 125 4222   | 20 10 001 4221 | 09 14 000 6111  | 09 14 000 6121  |

|                    |                       |                |                  |                |
|--------------------|-----------------------|----------------|------------------|----------------|
| Series             | Han® Pneumatic module |                |                  |                |
| Number of contacts | 2                     |                | 3                |                |
| Modules            |                       |                |                  |                |
| Male insert (M)    | 09 14 002 4501        |                | 09 14 003 4501   |                |
| Female insert (F)  | 09 14 002 4501        |                | 09 14 003 4501   |                |
| Contacts           | without shut off      | with shut off  | without shut off | with shut off  |
|                    |                       |                |                  |                |
|                    | Ø 6.0 mm              | Ø 6.0 mm       | Ø 1.6 mm         | Ø 1.6 mm       |
| Male contact       | 09 14 000 6174        |                | 09 14 000 6151   |                |
| Female contact     | 09 14 000 6274        | 09 14 000 6276 | 09 14 000 6251   | 09 14 000 6256 |

|                    |                       |                |                  |                |
|--------------------|-----------------------|----------------|------------------|----------------|
| Series             | Han® Pneumatic module |                |                  |                |
| Number of contacts | 3                     |                |                  |                |
| Modules            |                       |                |                  |                |
| Male insert (M)    | 09 14 003 4501        |                |                  |                |
| Female insert (F)  | 09 14 003 4501        |                |                  |                |
| Contacts           | without shut off      | with shut off  | without shut off | with shut off  |
|                    |                       |                |                  |                |
|                    | Ø 3.0 mm              | Ø 3.0 mm       | Ø 4.0 mm         | Ø 4.0 mm       |
| Male contact       | 09 14 000 6152        |                | 09 14 000 6153   |                |
| Female contact     | 09 14 000 6252        | 09 14 000 6253 | 09 14 000 6257   | 09 14 000 6258 |