

Series	Han® SC module			
Number of contacts	4			
Modules				
Male insert (M)	09 14 004 4701			
Female insert (F)	09 14 004 4711			
Contacts	SC contact			
	for GI fibre 50/125 µm or 62.5/125 µm ceramic ferrule	for SI fibre (HCS®) 200/230 µm	with quick assembly technique for 1 mm POF	with crimp technique for 1 mm POF
Male contact	20 10 125 5211	20 10 230 5211	20 10 001 5217	20 10 001 5211

Series	Han-Elisa®				
Modules	Temperature module Pt100	Temperature module Pt100	Output module current	Output module voltage	Electronic identification module
	Measuring range 0 ... 100 °C	Measuring range 0 ... 200 °C	Output signal 4 ... 20 mA	Output signal 0 ... 10 V	
Male insert (M)	20 75 108 1101	20 75 108 1103			20 70 001 1001
Female insert (F)			20 75 104 2201	20 75 105 2201	

Series	Dummy module			
Modules				
	09 14 000 9950			