



Part-Number 09 99 000 0850

Features

- Closed hydraulic jack, hinged and rotatable
- Rotatable hydraulic cylinder and lithium-ion battery
- Integrated pressure measuring with optical and acoustic signal in case of failure
- Ergonomic two component plastic housing with soft inlays for comfortable and safe handling
- Automatic flyback after crimping

Included with the set

- The tool comes in a plastic case with enough space for crimp dies
- HARTING Battery-Hydraulic Crimp Tool 6 – 70 mm²
- Lithium-ion battery 18 V / 1.3 Ah (23.4 Wh)
- Battery charger for 18 V lithium-ion rechargeable batteries

Technical characteristics

- Crimping force: 60 kN
- Idle stroke: 17.5 mm
- Crimp wire gauge range: 6 – 70 mm²
- Rechargeable battery voltage: 18 V
- Rechargeable battery capacity: 1.3 Ah
- Charging time: 15 min
- Weight with rechargeable battery: 3.0 kg

Suitable for

- Compatible with all HARTING crimp dies for 60 kN tools as well as with the respective contacts
 - TC 70
 - TC 100
 - TC 200
 - TC 250
 - TC 350 up to 70 mm²
 - TC 650 up to 70 mm²