





Number of contacts

# 3

40 A 690 V 8 kV 3

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)																								
		Male	Female																									
Han-Modular®, Han® C module, Crimp termination  <p>Please order crimp contacts separately.</p>	1.5 ... 6	09 14 003 3001	09 14 003 3101	 <p>Contact arrangement (view from termination side)</p>																								
Han® C HMC, Crimp contact, Contact surface: HMC gold plated 	1.5 2.5 4 6 10	09 32 200 6114 09 32 200 6115 09 32 200 6119 09 32 200 6118 09 32 200 6117	09 32 200 6224 09 32 200 6225 09 32 200 6229 09 32 200 6228 09 32 200 6227	 <table border="1"> <thead> <tr> <th>Wire gauge</th> <th></th> <th>ø</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>1.5 mm<sup>2</sup></td> <td>AWG 16</td> <td>1.75 mm</td> <td>9.5 mm</td> </tr> <tr> <td>2.5 mm<sup>2</sup></td> <td>AWG 14</td> <td>2.25 mm</td> <td>9.5 mm</td> </tr> <tr> <td>4 mm<sup>2</sup></td> <td>AWG 12</td> <td>2.85 mm</td> <td>9.5 mm</td> </tr> <tr> <td>6 mm<sup>2</sup></td> <td>AWG 10</td> <td>3.5 mm</td> <td>9.5 mm</td> </tr> <tr> <td>10 mm<sup>2</sup></td> <td>AWG 8</td> <td>4.3 mm</td> <td>15 mm</td> </tr> </tbody> </table>	Wire gauge		ø	Stripping length	1.5 mm <sup>2</sup>	AWG 16	1.75 mm	9.5 mm	2.5 mm <sup>2</sup>	AWG 14	2.25 mm	9.5 mm	4 mm <sup>2</sup>	AWG 12	2.85 mm	9.5 mm	6 mm <sup>2</sup>	AWG 10	3.5 mm	9.5 mm	10 mm <sup>2</sup>	AWG 8	4.3 mm	15 mm
Wire gauge		ø	Stripping length																									
1.5 mm <sup>2</sup>	AWG 16	1.75 mm	9.5 mm																									
2.5 mm <sup>2</sup>	AWG 14	2.25 mm	9.5 mm																									
4 mm <sup>2</sup>	AWG 12	2.85 mm	9.5 mm																									
6 mm <sup>2</sup>	AWG 10	3.5 mm	9.5 mm																									
10 mm <sup>2</sup>	AWG 8	4.3 mm	15 mm																									

Han  
HMC