

Standard hoods/housings for industrial connectors
Double locking lever



Accessories

Features


- Allows the entry of pre-assembled cables into a switch cabinet
- Robust design
- High pole cable entry seals for up to 10 different cables
- For sealing and feed through of pre-assembled cables

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Material (hood/housing)	Aluminium die-cast
Material (seal)	NBR
RoHS	compliant

Specifications and approvals



Identification	Cable entry	Size	Part number High construction	Drawing (dimensions in mm)
Han® B, Panel feed through housing, Top entry, IP65 Pack contents: 2 split hood halves, 2x M4 screw  Please order cable entry seals separately.	2x 3x	10 B 16 B	09 30 010 0498 09 30 016 0498	