



Technical characteristics

Degree of protection acc. to IEC IP68
60529

Technical characteristics

Material (cable glands)
RoHS

Metal
compliant with exemption

Identification	Size	Clamping range (mm)	Part number	Drawing (dimensions in mm)			
				Outer cable Ø	SW	E	Shielding Ø B
Cable gland, EMC version, IP68	M20	4 ... 6.5	19 62 000 5081	6.5 ... 9.5	22	24.4	3.5 ... 8.5
	M20	6.5 ... 9.5	19 62 000 5080	4 ... 6.5	22	24.4	2.5 ... 6.5
	M20	7 ... 10.5	19 62 000 5082	7 ... 10.5	22	24.4	6.5 ... 10.5
	M20	9 ... 13	19 62 000 5084	9 ... 13	22	24.4	6.5 ... 10.5
	M25	6.5 ... 9.5	19 62 000 5090	6.5 ... 9.5	22	31.2	3 ... 8
	M25	9 ... 13	19 62 000 5092	9 ... 13	28	31.2	4.8 ... 8
	M32	11.5 ... 15.5	19 62 000 5094	11.5 ... 15.5	35	38.5	8 ... 13.5
	M32	14 ... 18	19 62 000 5096	14 ... 18	35	38.5	9 ... 14.5
	M40	17 ... 20.5	19 62 000 5097	17 ... 20.5	43	47.3	15 ... 20
	M40	20 ... 25	19 62 000 5098	20 ... 25	43	47.3	15 ... 20

