

Tools

## Details

The high end tool with best performance.

## Details

for wire gauges from 0.14 und 0.25 mm<sup>2</sup> please use the contacts 09 15 000 6107, 6207, 6127 or 6227.

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number	
Crimping tool, Han D®: 0.14 ... 2.5 mm <sup>2</sup> , Han E®: 0.14 ... 4 mm <sup>2</sup> , Han-Yellok®: 0.14 ... 4 mm <sup>2</sup> , Han® C: 1.5 ... 4 mm <sup>2</sup> , Pack contents: incl. locator, Handling instruction		09 99 000 0888	
Check gauge, for crimping tool 09 99 000 0888, for optional testing		09 99 000 0889	
Locator, Spare part, for crimping tool 09 99 000 0888		09 99 000 0887	
Locator, Han E®, Relay contacts	0.14 ... 4	09 99 000 0978	