




PCB distance	Type	Pictures	Number of contacts	Performance level	Female			Male			
					Termination length (mm)	Termination*	Part number	Part number	Termination*	Termination length (mm)	
14.7 - 16.7 mm	SEK		6	PL2	2.9	THT THR	09 19 506 6824	09 18 506 6324 09 19 506 6324	THT THR	2.9	
						THR (T&R)	09 19 506 6824741	09 19 506 6324740 09 19 506 6324741	THR (T&R)		
					4.5	THT THR	09 19 506 6822	09 18 506 6322 09 19 506 6322	THT THR	4.5	
				Press-in	09 19 506 6829	09 18 506 6329	Press-in	5.5			
				PL3	2.9	THT THR	09 19 506 7824	09 18 506 7324 09 19 506 7324	THT THR	2.9	
						THR (T&R)	09 19 506 7824741	09 19 506 7324740 09 19 506 7324741	THR (T&R)		
			4.5		THT THR	09 19 506 7822	09 18 506 7322 09 19 506 7322	THT THR	4.5		
			Press-in	09 19 506 7829	09 18 506 7329	Press-in	5.5				
				10	PL2	2.9	THT THR	09 19 510 6824	09 18 510 6324 09 19 510 6324	THT THR	2.9
							THR (T&R)	09 19 510 6824741	09 19 510 6324740 09 19 510 6324741	THR (T&R)	
						4.5	THT THR	09 19 510 6822	09 18 510 6322 09 19 510 6322	THT THR	4.5
					Press-in	09 19 510 6829	09 18 510 6329	Press-in	5.5		
		PL3			2.9	THT THR	09 19 510 7824	09 18 510 7324 09 19 510 7324	THT THR	2.9	
						THR (T&R)	09 19 510 7824741	09 19 510 7324740 09 19 510 7324741	THR (T&R)		
				4.5	THT THR	09 19 510 7822	09 18 510 7322 09 19 510 7322	THT THR	4.5		
		Press-in		09 19 510 7829	09 18 510 7329	Press-in	5.5				
				14	PL2	2.9	THT THR	09 19 514 6824	09 18 514 6324 09 19 514 6324	THT THR	2.9
							THR (T&R)	09 19 514 6824741	09 19 514 6324740 09 19 514 6324741	THR (T&R)	
						4.5	THT THR	09 19 514 6822	09 18 514 6322 09 19 514 6322	THT THR	4.5
					Press-in	09 19 514 6829	09 18 514 6329	Press-in	5.5		
			PL3		2.9	THT THR	09 19 514 7824	09 18 514 7324 09 19 514 7324	THT THR	2.9	
						THR (T&R)	09 19 514 7824741	09 19 514 7324740 09 19 514 7324741	THR (T&R)		
				4.5	THT THR	09 19 514 7822	09 18 514 7322 09 19 514 7322	THT THR	4.5		
			Press-in	09 19 514 7829	09 18 514 7329	Press-in	5.5				

*Terminations: THT = through hole technology (Wave Solder); THR = through hole reflow; T&R = tape&reel packaging