



Number of contacts

24 + 

500 V 16 A





Identification	Part number		Drawing	Dimensions in mm
	Male insert (M)	Female insert (F)		


Han® 24 ES Press

09 33 024 2648

09 33 024 2748




1) Distance for contacts max. 21 mm



M

F

Contact arrangement: view from termination side



Panel cut out