

Number of contacts

# 4

48 V  
12 A



## Features

- One connection for the power input, the power output and to connect with the device
- Compact, space-saving design
- Finger safe acc. to IEC DIN EN 60 529
- Polarisation with the aid of coding pins
- Cable side: Male with crimp termination
- 4 different coding variants without loss of contact

## Technical characteristics

Contacts	4
Electrical data acc. to IEC 61 948	<b>12 A 48 V 1.5 kV 3</b>
Rated current	12 A
Rated voltage	48 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Insulation resistance	≥ 10 <sup>10</sup> Ω hm
Flammability acc. to UL 94	V 0
Mating cycles	≥ 750
Degree of protection acc. to IEC DIN EN 60 529	IP65 / IP67
Material hoods/housings	polyamide
Colour hoods/housings	RAL 9005 (black)

Identification

Part number

Drawing

Dimensions in mm

Han-Power® T with  
3 x HARTING PushPull Power

09 12 008 4770

