



## Han® F+B Ethernet connector for food industry

Identification	Part number	Drawing	Dimensions in mm
<b>Han® 3 A RJ45 connector inserts</b> <span style="float: right;">①</span> Cat. 5, 4 poles, 10/100 Mbit/s IDC for AWG 24-22 solid and stranded Cat. 5, 4 poles, 10/100 Mbit/s IDC for AWG 26-24 solid and stranded Cat. 6, 8 poles, 10/100 Mbit/s and 1/10 Gbit/s IDC for AWG 27-22 solid and stranded Cat. 6 <sub>A</sub> , 8 poles, 10/100 Mbit/s and 1/10 Gbit/s piercing termination for AWG 28-26 stranded Cat. 6 <sub>A</sub> , 8 poles, 10/100 Mbit/s and 1/10 Gbit/s preLink® IDC for AWG 23/22 or AWG 27/26 depending on the separately orderable preLink® terminal module (20 82 000 0001/20 82 000 0003)	09 45 100 1100 09 45 100 1110 09 45 100 1560 09 45 100 1520 20 82 002 0001		
<b>Han® F+B adapter for Han® 3 A inserts</b> <span style="float: right;">②</span>	09 15 503 9911		
<b>Han® F+B connector housing M25</b> <span style="float: right;">③</span>	19 15 503 1401		
<b>Han® F+B cable glands</b> <b>M25 cable glands plastic</b> Sealing range 5 – 9 mm Sealing range 9 – 16 mm Sealing range 13 – 18 mm  Needed lock cover (to avoid dirtiness areas at the cable gland) 1.2 mm thickness 2.5 mm thickness	19 00 000 5189 19 00 000 5191 19 00 000 5193  09 15 500 9912 09 15 500 9911		
<b>Accessories</b> Protection cap for Han® F+B connector housing	09 15 503 5411		