



Identification	Plastic version	Part number Metal version	Metal, overmoulded
Han® PushPull RJ45 system cable, 4-wire Type B			
Length 1.5 m	09 47 555 5033	09 47 565 6033	09 47 565 7033
3.0 m	09 47 555 5035	09 47 565 6035	09 47 565 7035
5.0 m	09 47 555 5037	09 47 565 6037	09 47 565 7037
10.0 m	09 47 555 5042	09 47 565 6042	09 47 565 7042
20.0 m	09 47 555 5044	09 47 565 6044	09 47 565 7044
Han® PushPull RJ45 system cable, 4-wire Type C			
Length 1.5 m	09 47 555 5063	09 47 565 6063	09 47 565 7063
3.0 m	09 47 555 5065	09 47 565 6065	09 47 565 7065
5.0 m	09 47 555 5067	09 47 565 6067	09 47 565 7067
10.0 m	09 47 555 5072	09 47 565 6072	09 47 565 7072
20.0 m	09 47 555 5074	09 47 565 6074	09 47 565 7074
Han® PushPull RJ45 system cable, 4-wire Outdoor			
Length 1.5 m	09 47 555 5093	09 47 565 6093	09 47 565 7093
3.0 m	09 47 555 5095	09 47 565 6095	09 47 565 7095
5.0 m	09 47 555 5097	09 47 565 6097	09 47 565 7097
10.0 m	09 47 555 5102	09 47 565 6102	09 47 565 7102
20.0 m	09 47 555 5104	09 47 565 6104	09 47 565 7104

Other cable lengths on request