

DIRECT DEVICE INTEGRATION ON PCB			
	HARTING PushPull EasyInstall bulkhead housing for device integration	Metal, angled, without fixing clip Metal, angled, with fixing clip	09 45 595 0030 09 45 595 0031
	HARTING PushPull Compact bulkhead housing for device integration	Plastic, angled, without fixing clip Plastic, angled, with fixing clip	09 45 545 0043 09 45 545 0042
	HARTING PushPull RJ45 jack, Cat. 5	angled SMD 90° angled SMD 90° T&R packaging angled 90°, THT straight 180°, THT	09 45 551 1100 09 45 551 1110 09 45 551 1102 09 45 551 1103
DEVICE INTEGRATION WITH PANEL FEED-THROUGH			
	HARTING PushPull RJ45 panel feed-through, metal	EasyInstall, Cat. 5	09 45 295 1130
	HARTING PushPull RJ45 panel feed-through, plastic	Compact, Cat. 6	09 45 245 1561
	HARTING PushPull RJ45 panel feed-through, plastic with cable jack	Compact housing Cable jack, 8 pole, Cat. 6, AWG 28 - 24, IDC Cable jack, 8 pole, Cat. 6, AWG 24 - 22, IDC preLink® cable jack, 8 pole, Cat. 6	09 45 545 0041 09 45 545 1561 09 45 545 1562 20 82 001 0002
CONNECTOR CABLE SIDE			
	HARTING PushPull RJ45 connector with IDC- or piercing termination, metal	4 poles, Cat. 5 IDC 8 poles, Cat. 6 _A 8 poles, Cat. 6 IDC	09 45 195 1100 09 45 195 1520 09 45 195 1560
	HARTING PushPull RJ45 connector with IDC- or piercing termination, plastic	4 poles, Cat. 5 IDC 8 poles, Cat. 6 _A 8 poles, Cat. 6 IDC	09 45 145 1106 09 45 145 1521 09 45 145 1561
SYSTEM CABLE PUR, RJ45, 8 POLES			
	HARTING PushPull system cable RJ45, 8 poles, Cat. 6, yellow, PUR cable 8x AWG 26/7 stranded (other cable types and length on request)	1.0 m 3.0 m 5.0 m 10.0 m	09 48 282 8756 010 09 48 282 8756 030 09 48 282 8756 050 09 48 282 8756 100
OUTLETS			
	HARTING PushPull RJ45 outlet, Cat. 6, 2 times	Plastic, black Plastic, white	09 45 845 1500 09 45 845 1501
	IP65 / IP67 HARTING PushPull RJ45 coupler, Cat.6	Plastic, black	09 45 345 1560
DIRECT DEVICE INTEGRATION ON PCB			
	Han® PushPull RJ45 bulkhead housing for device integration	Metal Plastic	09 35 002 0301 09 35 002 0321
	Han® PushPull RJ45 jack insert for PCB mounting, 8 poles, shielded, Cat. 6, with straight and angled solder pins	angled 90° straight 180°	09 35 002 2101 09 35 002 2102
DEVICE INTEGRATION WITH PANEL FEED-THROUGH			
	Han® PushPull RJ45, panel feed-through with RJ45 contact insert, 8 poles	Metal, straight, Cat. 6, rectangular Metal, straight, Cat. 6, circular Plastic, straight, Cat. 6	09 35 225 0311 09 35 225 0312 09 35 225 0331
	Han® PushPull RJ45, panel feed-through with cable jack	Metal housing, rectangular, HIFF Metal housing, circular, HIFF Plastic housing, rectangular, HIFF Cable jack, 8 pole, Cat. 6, AWG 28 - 24, IDC Cable jack, 8 pole, Cat. 6, AWG 24 - 22, IDC preLink® cable jack, 8 pole, Cat. 6	09 35 012 0311 09 35 012 0312 09 35 012 0331 09 45 545 1561 09 45 545 1562 20 82 001 0002

V4

V14