








CONNECTOR CABLE SIDE					
V14		Han® PushPull RJ45, connector, with IDC-, piercing or preLink® termination	Metal, RJ45 4 poles, Cat. 5 IDC Metal, RJ45 4 poles, Cat. 5, IDC, PROFINET Metal, RJ45 8 poles, Cat. 6A Metal, RJ45 8 poles, Cat. 6 IDC Metal, RJ45 8 poles, Cat. 6A preLink® Metal, angled, cable exit bottom, RJ45 8 poles, Cat. 6 IDC Metal, angled, cable exit top, RJ45 8 poles, Cat. 6 IDC Metal, angled, cable exit bottom, RJ45 8 poles, Cat. 6A preLink®	09 35 221 0401 09 35 226 0401 09 35 227 0401 09 35 225 0401 20 82 104 0001 09 35 225 0402 09 35 225 0403 20 82 104 0045	
		Han® PushPull RJ45, connector, with IDC-, piercing or preLink® termination	Plastic, RJ45 4 poles, 6.5 - 9.5 mm, IDC Plastic, RJ45 4 poles, 5 - 8 mm, IDC Plastic, RJ45 4 poles, Cat. 5, IDC, PROFINET Plastic, RJ45 8 poles, Cat. 6 Plastic, RJ45 8 poles, Cat. 6 IDC Plastic, RJ45 8 poles, Cat. 6A preLink®	09 35 221 0421 09 35 222 0421 09 35 226 0421 09 35 227 0421 09 35 225 0421 20 82 204 0001	
ACCESSORIES					
		Han® PushPull RJ45, gender changer / cable coupling, 8 poles, Cat. 6, class EA	Gender changer RJ45, metal Cable coupling, metal	09 35 221 0501 61 04 201 1084	
SYSTEM CABLE					
		Han® PushPull system cable RJ45, 4 poles, green, copper, shielded, Cat. 5, 10/100 Mbit/s (other cable types and lengths on request)	Length	Metal	Plastic
		Type A, outer jacket PVC	3.0 m	09 47 565 6005	09 47 555 5005
		Type B, outer jacket PVC	3.0 m	09 47 565 6035	09 47 555 5035
		Type C, outer jacket PUR	3.0 m	09 47 565 6065	09 47 555 5065

TOOLING				
V4 V14		HARTING RJ Industrial® stripping tool	Stripping for Ethernet cable inclusive blade cassette	09 45 800 0000
			Blade cassette	09 45 800 0001
		HARTING RJ Industrial® universal stripping tool		09 45 800 0002
		HARTING RJ Industrial® cable cutter		09 45 800 0004
		HARTING RJ Industrial® side cutter		09 45 800 0005
		HARTING RJ Industrial® Gigalink mounting tool	for HARTING RJ Industrial® Gigalink connectors	09 45 800 0520
preLink® mounting tool	for preLink® connectors	20 82 000 9901		

DEVICE INTEGRATION WITH PANEL FEED-THROUGH					
V4		HARTING PushPull LC duplex panel feed-through	Metal, multimode GOF EasyInstall Metal, singlemode GOF EasyInstall Plastic, multimode GOF Compact Plastic, singlemode GOF Compact	09 57 468 0500 000 09 57 468 0501 000 09 57 442 0511 000 09 57 442 0512 000	
	SYSTEM CABLE				
		HARTING PushPull LC duplex system cable Other cable types and length on request	Length	Metal	Plastic
			1.0 m singlemode	33 58 231 0010 026	33 61 221 0010 001
			1.0 m multimode 50 / 125	33 58 231 0010 027	33 61 221 0010 002
			1.0 m multimode 62.5 / 125	33 58 231 0010 028	33 61 221 0010 003
			10.0 m singlemode	33 58 231 0100 026	33 61 221 0100 001
			10.0 m multimode 50 / 125	33 58 231 0100 027	33 61 221 0100 002
			10.0 m multimode 62.5 / 125	33 58 231 0100 028	33 61 221 0100 003