














V14

DIRECT DEVICE INTEGRATION ON PCB			
	Han® PushPull SCRJ bulkhead housing for device integration	Metal Plastic	09 35 002 0303 09 35 002 0323
DEVICE INTEGRATION WITH PANEL FEED-THROUGH			
	Han® PushPull SCRJ panel feed-through, duplex, for multimode-glass, HCS- and polymer fibres	Metal, optical panel feed-through Plastic, optical panel feed-through	09 35 242 0313 09 35 242 0333
CONNECTOR CABLE SIDE			
	Han® PushPull SCRJ connector, duplex, for multimode-glass, HCS- and polymer fibres	Metal, inclusive 2x SC POF contacts Metal, order SC contacts separately Metal, inclusive 2x SC POF crimp contacts Plastic, inclusive 2x SC POF contacts Plastic, order SC contacts separately	09 35 241 0401 09 35 241 0402 09 35 242 0401 09 35 241 0421 09 35 241 0422
	IP20 SCRJ POF connector, duplex, plastic	inclusive 2x SC POF contacts inclusive 2x SC POF contacts, crimp	09 35 002 4002 09 35 002 4003
TOOLING			
	Mounting case POF, cutting without polishing	for field termination of SC-POF contacts for field termination of SC-crimp contacts  Replacement cutting tool	09 35 000 9913 09 35 000 9915  09 35 000 9914
SYSTEM CABLE			
	IP20 cable assembly, round cable, green, outer jacket PUR, both sides assembled with SCRJ IP20 connector (other cable types and lengths on request)	1.0 m 2.0 m 5.0 m 10.0 m 20.0 m	33 02 211 0010 001 33 02 211 0020 001 33 02 211 0050 001 33 02 211 0100 001 33 02 211 0200 001
	Cable assembly, round cable, green, outer jacket PUR, both sides IP65 / IP67, plastic version (other cable types and lengths on request)	1.0 m 2.0 m 5.0 m 10.0 m 20.0 m	33 53 211 0010 001 33 53 211 0020 001 33 53 211 0050 001 33 53 211 0100 001 33 53 211 0200 001
	Cable assembly, round cable, green, outer jacket PUR, both sides IP65 / IP67, metal version (other cable types and lengths on request)	1.0 m 2.0 m 5.0 m 10.0 m 20.0 m	33 53 211 0010 002 33 53 211 0020 002 33 53 211 0050 002 33 53 211 0100 002 33 53 211 0200 002

V4

DIRECT DEVICE INTEGRATION ON PCB			
	HARTING PushPull Compact bulkhead housing for device integration	Plastic, angled, without fixing clip Plastic, angled, with fixing clip	09 45 545 0043 09 45 545 0042
	HARTING PushPull USB solder jack, angled 90°, THT	USB 2.0 type B	09 45 541 1900
	HARTING PushPull USB adapter PCB	USB 2.0 type A to pin header USB 2.0 type A to solder points USB 2.0 type B-B USB 2.0 type B-B, 90° USB 2.0 type A-B	09 45 541 1902 09 45 541 1903 09 45 541 1906 09 45 541 1907 09 45 541 1910
DEVICE INTEGRATION WITH PANEL FEED-THROUGH			
	HARTING PushPull USB Compact, panel feed-through, jack to jack	USB 2.0 type A USB 3.0 type A	09 45 245 1920 09 45 245 1930
SYSTEM CABLE			
	HARTING PushPull USB shielded system cable (other cable types and lengths on request)	USB 2.0 type B, double sided PushPull 1.5 m USB 2.0 type A, double sided PushPull 1.5 m USB 3.0 type A, double sided PushPull 1.5 m	09 45 445 3902 09 45 445 1902 09 45 445 2902
		USB 2.0 type B, PushPull - IP20 1.5 m USB 2.0 type A, PushPull - IP20 1.5 m USB 3.0 type A, PushPull - IP20 1.5 m	09 45 445 3912 09 45 445 1912 09 45 445 2912