







DIRECT DEVICE INTEGRATION ON PCB			
	Han® PushPull Power bulkhead housing for device integration	Metal Plastic	09 35 002 0303 09 35 002 0323
	Han® PushPull Power, jack insert for PCB mounting, 5 poles, 16 A, 230/400 V, with straight and angled solder pins	angled 90° straight 180°	09 35 002 3003 09 35 002 3004
DEVICE INTEGRATION WITH PANEL FEED-THROUGH			
	Han® PushPull Power, panel feed-through, 5 poles, 16 A, 690 V, with crimp or Quick Lock®-termination, touch-proof, 4 times codeable, order Han® P male crimp contacts separately	Metal, crimp termination – rectangular cut-out Metal, Quick Lock® termination, 0.5 ... 2.5 mm <sup>2</sup> Metal, Quick Lock® termination, 0.25 ... 1.5 mm <sup>2</sup> Metal, crimp termination – circular cut-out Metal, Quick Lock® termination, 0.5 ... 2.5 mm <sup>2</sup> Metal, Quick Lock® termination, 0.25 ... 1.5 mm <sup>2</sup>	09 35 231 0311 09 35 232 0311 09 35 234 0311 09 35 231 0312 09 35 232 0312 09 35 234 0312
		Plastic, crimp termination – rectangular cut-out Plastic, Quick Lock® termination, 0.5 ... 2.5 mm <sup>2</sup> Plastic, Quick Lock® termination, 0.25 ... 1.5 mm <sup>2</sup> Plastic, crimp termination – circular cut-out Plastic, Quick Lock® termination, 0.5 ... 2.5 mm <sup>2</sup> Plastic, Quick Lock® termination, 0.25 ... 1.5 mm <sup>2</sup>	09 35 231 0331 09 35 232 0331 09 35 234 0331 09 35 231 0332 09 35 232 0332 09 35 234 0332
CONNECTOR CABLE SIDE			
	Han® PushPull Power, connector, 5 poles, 16 A, 690 V, with crimp or Quick Lock®-termination, cable diameter 4-11 mm (metal), 6.5-9.5 / 9-13 mm (plastic), touch-proof, 4 times codeable, order Han® P female crimp contacts separately	Metal, crimp termination Metal, Quick Lock® termination, 0.5 ... 2.5 mm <sup>2</sup> Metal, Quick Lock® termination, 0.25 ... 1.5 mm <sup>2</sup>	09 35 231 0401 09 35 232 0401 09 35 234 0401
		Plastic, crimp termination, 6.5 - 9.5 mm Plastic, crimp termination, 9 - 13 mm Plastic, Quick Lock® termination, 6.5 - 9.5 mm, 0.5 ... 2.5 mm <sup>2</sup> Plastic, Quick Lock® termination, 6.5 - 9.5 mm, 0.25 ... 1.5 mm <sup>2</sup> Plastic, Quick Lock® termination, 9 - 13 mm, 0.5 ... 2.5 mm <sup>2</sup>	09 35 231 0421 09 35 231 0423 09 35 232 0421 09 35 234 0421 09 35 232 0423
ACCESSORIES			
	Han® PushPull Power coding key set, 4 times codeable, set includes 10 pieces for device and cable side each	Coding keys	09 35 000 6190
	Han® P male crimp contacts for Han® PushPull Power panel feed-through	for 0.5 mm <sup>2</sup> for 0.75 mm <sup>2</sup> for 1.0 mm <sup>2</sup> for 1.5 mm <sup>2</sup> for 2.5 mm <sup>2</sup>	09 35 000 6103 09 35 000 6104 09 35 000 6105 09 35 000 6106 09 35 000 6107
		Han® P female crimp contacts for Han® PushPull Power connector	for 0.5 mm <sup>2</sup> for 0.75 mm <sup>2</sup> for 1.0 mm <sup>2</sup> for 1.5 mm <sup>2</sup> for 2.5 mm <sup>2</sup>

DEVICE INTEGRATION WITH PANEL FEED-THROUGH			
	Han® PushPull Power L bulkhead housing for device integration	Metal	09 35 014 0301
	Han® PushPull Power L, panel feed-through, 5 poles, 16 A, 24 V, spring-cage connection, 0.75 - 2.5 mm <sup>2</sup> , touch-proof	Metal, fixed coding, 24 V acc. PNO Guideline Metal, variable coding	09 35 433 0311 09 35 434 0311
CONNECTOR CABLE SIDE			
	Han® PushPull Power L, connector, 5 poles, 16 A, 24 V, spring-cage connection, 0.75 - 2.5 mm <sup>2</sup> , touch-proof	Metal, fixed coding, 24 V acc. PNO Guideline, 9 - 13 mm Metal, fixed coding, 24 V acc. PNO Guideline, 6 - 10 mm Metal, variable coding, 9 - 13 mm	09 35 433 0401 09 35 433 0441 09 35 434 0401
ACCESSORIES			
	Han® PushPull Power L, gender changer, cable coupling, 5 poles, 16 A, 24 V	Gender changer Power L Cable coupling, metal	09 35 431 0501 61 04 201 1085
	Han® PushPull Power L, protection cover IP65 / IP67	for bulkhead housing for cable side	09 35 004 5402 09 35 004 5412
	Separate seal for Han® PushPull Power L connector	4 - 6.5 mm 6 - 10 mm	09 35 004 9907 09 35 004 9908