

preLink® displacement termination





### Technical characteristics

Limiting temperature	-40 ... +85 °C
Mating cycles	≥ 10
Wire outer diameter	1.3 ... 1.6 mm, 0.8 ... 1.1 mm
Conductor cross-section	0.22 ... 0.32 mm <sup>2</sup> , 0.1 ... 0.12 mm <sup>2</sup>
Conductor cross-section	AWG 24 ... AWG 22, AWG 27... AWG 26
Colour (insert)	Yellow, White, Black
RoHS	compliant

### Specifications and approvals

DNV GL  
 UL 1863 DUXR2.E470046  
 CSA-C22.2 No. 182.4,  
 No. 233-09 DUXR8.E470046



Identification	Conductor cross-section (mm <sup>2</sup> )	Path number	Drawing	Dimensions in mm
preLink®, Terminal module, 8-pins, preLink® IDC insulation displacement termination, Conductor diameter 1.3 - 1.6 mm,  Pack contents: 10 pieces 	0.22 ... 0.32	20 82 000 0001		
preLink®, Terminal module, 8-pins, preLink® IDC insulation displacement termination, Conductor diameter 0.8 - 1.1 mm,  Pack contents: 10 pieces 	0.1 ... 0.12	20 82 000 0003	