



Han® PushPull,  
type acc. to IEC 61076-3-117 variant 14  
Housing bulkhead mounting and housing cable-to-cable combinations

Identification	Part number	Drawing	Dimensions in mm
<b>RJ45 female inserts</b> <span style="float: right;">②</span>  Cat. 5, 4 poles, 10 Mbit/s, 100 Mbit/s IDC for AWG 24-22 solid and stranded  Cat. 6 <sub>A</sub> , 8 poles, 10 Mbit/s, 100 Mbit/s and 1 Gbit/s, 10 Gbit/s IDC for AWG 28-24 solid and stranded  Cat. 6 <sub>A</sub> , 8 poles, 10 Mbit/s, 100 Mbit/s and 1 Gbit/s, 10 Gbit/s IDC for AWG 24-22 solid and stranded  Cat. 6 <sub>A</sub> , 8 poles, 10 Mbit/s, 100 Mbit/s and 1 Gbit/s, 10 Gbit/s preLink® IDC for AWG 23/22 solid and stranded  Cat. 6 <sub>A</sub> , 8 poles, 10 Mbit/s, 100 Mbit/s and 1 Gbit/s, 10 Gbit/s preLink® IDC for AWG 27/26 solid and stranded  Cat. 6 <sub>A</sub> , 8 poles, 10 Mbit/s, 100 Mbit/s and 1 Gbit/s, 10 Gbit/s preLink® IDC for AWG 23/22 or AWG 27/26 depending on the separately orderable preLink® terminal module (20 82 000 0001/20 82 000 0003)	09 45 545 1120  09 45 545 1561  09 45 545 1562  20 82 001 0001  20 82 001 0002  20 82 000 0002		
<b>Han® PushPull Housing cable-to-cable</b> <span style="float: right;">③</span>  plastic, black (not in combination with Housing bulkhead mounting 09 35 012 0312!)  for cable outer diameter 6.5 ... 9.5 mm  for cable outer diameter 9 ... 13 mm	09 35 002 0431  09 35 002 0433		