





## Han® 3 A RJ45 panel feed-throughs

Identification	Part number	Drawing	Dimensions in mm
<b>Han® 3 A RJ45 female inserts</b> <span style="float: right;">①</span>  Cat. 5, 4 poles, 10 Mbit/s, 100 Mbit/s IDC for AWG 24-22 solid and stranded  Cat. 6A, 8 poles, 10 Mbit/s, 100 Mbit/s and 1 Gbit/s 10 Gbit/s IDC for AWG 28-24 solid and stranded  Cat. 6A, 8 poles, 10 Mbit/s, 100 Mbit/s and 1 Gbit/s 10 Gbit/s IDC for AWG 24-22 solid and stranded  Cat. 6A, 4/8 poles, 10 Mbit/s, 100 Mbit/s and 1 Gbit/s 10 Gbit/s preLink® IDC for AWG 23/22 or AWG 27/26 depending on the separately orderable preLink® terminal module (20 82 000 0001/20 82 000 0003)  Cat. 6, 8 poles, 10 Mbit/s, 100 Mbit/s and 1 Gbit/s, 10 Gbit/s RJ45 system cable jack on connector  0.15 m ... 10.0 m   Cat. 6, 8 poles, 10 Mbit/s, 100 Mbit/s and 1 Gbit/s, 10 Gbit/s RJ45 coupler with Han® 3 A adapter  	09 45 545 1120  09 45 545 1561  09 45 545 1562  20 82 001 0001     09 45 545 1500  ... 09 45 545 1518   09 45 200 1560	    	
<b>Han® 3 A adapter for HIFF inserts</b> <span style="float: right;">②</span>	09 45 515 0024		