



har-port RJ45 coupler

Identification	Part number	Drawing	Dimensions in mm
RJ45 female inserts ② Cat. 5, 4 poles, 10 Mbit/s, 100 Mbit/s IDC for AWG 24-22 solid and stranded 09 45 545 1120 Cat. 6A, 8 poles, 10 Mbit/s, 100 Mbit/s and 1 Gbit/s, 10 Gbit/s IDC for AWG 28-24 solid and stranded 09 45 545 1561 Cat. 6A, 8 poles, 10 Mbit/s, 100 Mbit/s and 1 Gbit/s, 10 Gbit/s IDC for AWG 24-22 solid and stranded 09 45 545 1562 Cat. 6A, 8 poles, 10 Mbit/s, 100 Mbit/s and 1 Gbit/s, 10 Gbit/s preLink® IDC for AWG 23/22 solid and stranded 20 82 001 0001 Cat. 6A, 8 poles, 10 Mbit/s, 100 Mbit/s and 1 Gbit/s, 10 Gbit/s preLink® IDC for AWG 27/26 solid and stranded 20 82 001 0002 Cat. 6A, 8 poles, 10 Mbit/s, 100 Mbit/s and 1 Gbit/s, 10 Gbit/s preLink® IDC for AWG 23/22 or AWG 27/26 depending on the separately orderable preLink® terminal module (20 82 000 0001/20 82 000 0003) 20 82 000 0002 preLink® terminal module gelb für AWG 23/22 solid and stranded 20 82 000 0001 preLink® terminal module weiß für AWG 27/26 solid and stranded 20 82 000 0003			
Accessories Unlocking tool for opening of the jacks 20 82 000 9916 preLink® assembly tool 20 82 000 9901			