



Han® F+B Ethernet connector for food industry

Identification	Part number	Drawing	Dimensions in mm
Han® 3 A RJ45 connector inserts ① Cat. 5, 4 poles, 10 Mbit/s, 100 Mbit/s IDC for AWG 24-22 solid and stranded Cat. 5, 4 poles, 10 Mbit/s, 100 Mbit/s IDC for AWG 26-24 solid and stranded Cat. 6, 8 poles, 10 Mbit/s, 100 Mbit/s and 1 Gbit/s, 10 Gbit/s IDC for AWG 27-22 solid and stranded Cat. 6 _A , 8 poles, 10 Mbit/s, 100 Mbit/s and 1 Gbit/s, 10 Gbit/s piercing termination for AWG 28-26 stranded Cat. 6 _A , 8 poles, 10 Mbit/s, 100 Mbit/s and 1 Gbit/s, 10 Gbit/s preLink® IDC for AWG 23/22 or AWG 27/26 depending on the separately orderable preLink® terminal module (20 82 000 0001/20 82 000 0003)	09 45 100 1100 09 45 100 1110 09 45 100 1560 09 45 100 1520 20 82 002 0001		
Han® F+B adapter for Han® 3 A inserts ②	09 15 503 9911		
Han® F+B connector housing M25 ③	19 15 503 1402		
Han® F+B cable glands M25 cable glands plastic Sealing range 5 – 8 mm	19 15 503 5290		
Accessories Protection cap for Han® F+B connector housing	09 15 503 5411		