

Accessories V4

Identification	Part number	Part number	Drawing	Dimensions in mm
HARTING PushPull Protection cover for Hybrid Signal, USB, RJ45, Power and LC duplex, device side, plastic Protection cover IP40 Protection cover IP65 / IP67, Version with passive locking without cord Version with passive locking with plastic cord for fixing screw Version with passive locking with nylon cord for fixing screw Version with active locking without cord Version with active locking with plastic cord for fixing screw Version with active locking with nylon cord for fixing screw	09 45 845 0003 000 09 45 845 0009 024 09 45 845 0009 000 09 45 845 0011 024 09 45 845 0015 000 09 45 845 0014 000 09 45 845 0013 000			
HARTING PushPull Protection cover for Hybrid Signal, USB, RJ45, Power and LC duplex, connectors, plastic Protection cover IP65 / IP67, with cord for fixing screw	09 45 845 0010 000			
HARTING PushPull Blinding plate	09 45 845 0019 000			
HARTING PushPull LC duplex Panel feed through metal, multi mode GOF EasyInstall metal, single mode GOF EasyInstall plastic, multi mode GOF Compact plastic, single mode GOF Compact	09 57 468 0500 000 09 57 468 0501 000 09 57 442 0511 000 09 57 442 0512 000			
HARTING PushPull LC duplex systems cable Other cable types on request Length:		Metal Plastic		
1.0 m single mode	33 58 231 0010 026	33 61 221 0010 001		
1.0 m multi mode 50 / 125	33 58 231 0010 027	33 61 221 0010 002		
1.0 m multi mode 62.5 / 125	33 58 231 0010 028	33 61 221 0010 003		
10.0 m single mode	33 58 231 0100 026	33 61 221 0100 001		
10.0 m multi mode 50 / 125	33 58 231 0100 027	33 61 221 0100 002		
10.0 m multi mode 62.5 / 125	33 58 231 0100 028	33 61 221 0100 003		