



HARTING M12
system cable, 4-wire,
straight resp. angled, Cat. 5

M12 cords

Identification		Part number	
		PUR	PVC
both sides assembled connector straight to connector straight	Length 0.5 m	21 34 929 2477 005	21 34 929 2405 005
	1.0 m	21 34 929 2477 010	21 34 929 2405 010
	1.5 m	21 34 929 2477 015	21 34 929 2405 015
	2.0 m	21 34 929 2477 020	21 34 929 2405 020
	5.0 m	21 34 929 2477 050	21 34 929 2405 050
	7.5 m	21 34 929 2477 075	21 34 929 2405 075
	10.0 m	21 34 929 2477 100	21 34 929 2405 100
both sides assembled connector straight to female angled	Length 0.5 m	21 34 929 3477 005	21 34 929 3405 005
	1.0 m	21 34 929 3477 010	21 34 929 3405 010
	1.5 m	21 34 929 3477 015	21 34 929 3405 015
	2.0 m	21 34 929 3477 020	21 34 929 3405 020
	5.0 m	21 34 929 3477 050	21 34 929 3405 050
	7.5 m	21 34 929 3477 075	21 34 929 3405 075
	10.0 m	21 34 929 3477 100	21 34 929 3405 100
one side assembled connector straight to open end	Length 0.5 m	21 34 920 0477 005	21 34 920 0405 005
	1.0 m	21 34 920 0477 010	21 34 920 0405 010
	1.5 m	21 34 920 0477 015	21 34 920 0405 015
	2.0 m	21 34 920 0477 020	21 34 920 0405 020
	5.0 m	21 34 920 0477 050	21 34 920 0405 050
	7.5 m	21 34 920 0477 075	21 34 920 0405 075
	10.0 m	21 34 920 0477 100	21 34 920 0405 100
one side assembled female straight to open end	Length 0.5 m	21 34 930 0477 005	21 34 930 0405 005
	1.0 m	21 34 930 0477 010	21 34 930 0405 010
	1.5 m	21 34 930 0477 015	21 34 930 0405 015
	2.0 m	21 34 930 0477 020	21 34 930 0405 020
	5.0 m	21 34 930 0477 050	21 34 930 0405 050
	7.5 m	21 34 930 0477 075	21 34 930 0405 075
	10.0 m	21 34 930 0477 100	21 34 930 0405 100
both sides assembled connector angled to connector angled	Length 0.5 m	21 34 949 4477 005	21 34 949 4405 005
	1.0 m	21 34 949 4477 010	21 34 949 4405 010
	1.5 m	21 34 949 4477 015	21 34 949 4405 015
	2.0 m	21 34 949 4477 020	21 34 949 4405 020
	5.0 m	21 34 949 4477 050	21 34 949 4405 050
	7.5 m	21 34 949 4477 075	21 34 949 4405 075
	10.0 m	21 34 949 4477 100	21 34 949 4405 100