

Summary shell housings and accessories



Appropriate connectors in shell housings	Types B, C, D, E, har-bus® 64	Types 2C, 3C	Type F	Types F, H, MH	Types E, F, H, MH
Check list: How to order shell housings and accessories. The Part number is stated.					
Shell housings	C 09 02 064 0501 09 02 064 0502 09 03 096 0501 09 05 048 0501	2C, 3C 09 23 048 0501 09 25 030 0501	A 09 06 048 0501 09 06 048 0402	B 09 06 048 0503 09 06 048 0504 09 06 048 0505	G 09 06 000 9957
Cable insert	09 02 000 9910 09 02 000 9911			09 06 000 9914 09 06 000 9915	
Insert for LED				09 06 000 9917	
Locking lever <small>Order 2 pieces, in some cases each with different Part Nos. for left and right hand</small>	09 02 000 9902 09 02 000 9903	Supplied with the shell housing	Supplied with the shell housing	09 06 000 9913 09 06 000 9919	
Locking screws <small>Order 2 sets</small>	for fixing elements with male connectors 09 02 000 9909 🔑 M 2.5 x 16 🌀 M 2.5	09 02 000 9909 🔑 M 2.5 x 16 🌀 M 2.5	🔑 M 2.5 x 12 🌀 M 2.5	09 06 000 9926 🔑 M 2.5 x 20 🌀 M 2.5	Supplied with the shell housing
	for interface connectors I 09 02 000 9909 🔑 M 2.5 x 16 🌀 M 2.5		🔑 M 2.5 x 22 Supplied with the interface connector I	09 06 000 9955 🔑 M 2.5 x 26	Supplied with the shell housing
Fixing brackets for 19" racks for male connectors	C 	C 	A 	B 	B
Multiple fixing	left 09 02 000 9919 right 09 02 000 9920	09 02 000 9919 09 02 000 9920	09 06 000 9901 09 06 000 9902	09 06 000 9907 09 06 000 9966 09 06 000 9908 09 06 000 9967	09 06 000 9907 09 06 000 9966 09 06 000 9908 09 06 000 9967
Single fixing	left 09 02 000 9921 right 09 02 000 9922	09 02 000 9921 09 02 000 9922	09 06 000 9905 09 06 000 9906	09 06 000 9909 09 06 001 9934 09 06 000 9910 09 06 001 9935	09 06 000 9909 09 06 001 9934 09 06 000 9910 09 06 001 9935
for female connectors				B 	
Multiple fixing	left right			09 06 000 9933 09 06 000 9933	
Fixing brackets for angled male connectors on pcb	C 	C 			
left	09 02 000 9926	09 02 000 9926			
right	09 02 000 9927	09 02 000 9927			
Fixing brackets for inverse male connectors on pcb	R 	R 			
R 1	09 02 000 9953	09 02 000 9953			
R 32	09 02 000 9954	09 02 000 9954			
Distance fixing brackets for piggyback connectors					
Type D top	09 04 000 9907				09 04 000 9907
Type E bottom	09 04 000 9906				09 04 000 9906
Type F top	09 06 000 9936				09 06 000 9936
bottom	09 06 000 9937				09 06 000 9937
Protection strip for 20 mm shell housing				09 06 000 9929	
Protection and fixing strip for 20 mm shell housing				09 06 001 9909	

Female connectors Male connectors

Detailed system description see chapter 00