

POWER (ACCESSORIES)	V4	TOOLING V4			
			HARTING PushPull Power crimping tool		09 46 800 0000
			Insertion and removal tools for HARTING PushPull Power contacts	Removal tool Insertion tool	09 46 800 0098 09 46 800 0099
			Locator for HARTING PushPull Power contacts	for use with crimping tool 09 99 000 0001	09 46 800 0010
	V14	TOOLING V14			
			Crimping tool	Wire gauge: 0.5 - 2.5 mm ²	09 99 000 0888
			Locator Han P®	for crimping tool	09 99 000 0886
			Multiple crimping tool depth adjustment gauge, wire gauge: 0.5 - 1 mm ² and 1.5 - 2.5 mm ²	for crimping tool	09 99 000 0379
			Removal tool Han P®	for Han P® contacts	09 99 000 0319
ACCESSORIES	V4	ACCESSORIES V4			
			HARTING PushPull protection covers for Hybrid Signal, USB, RJ45, Power and LC duplex, device side, plastic	Protection cover IP40	09 45 845 0003
				Protection cover IP65 / IP67, passive locking without fixing cord passive locking with plastic fixing cord passive locking with nylon fixing cord	09 45 845 0009 024 09 45 845 0009 09 45 845 0011 024
				Protection cover IP65 / IP67, active locking without fixing cord active locking with plastic fixing cord active locking with nylon fixing cord	09 45 845 0015 09 45 845 0014 09 45 845 0013
			HARTING PushPull protection covers for Hybrid Signal, USB, RJ45, Power and LC duplex, connector, plastic	Protection cover IP65 / IP67, with fixing cord	09 45 845 0010
			HARTING PushPull housings, plastic	Cable to cable, cable diameter 6.5 - 9.5 mm Bulkhead	09 45 345 0000 09 45 345 0001
			HARTING PushPull blinding plate		09 45 845 0019
			HARTING PushPull bulkhead, plastic, black	for an easy connection of PushPull RJ45 system cords	09 45 345 1560
	V14	ACCESSORIES V14			
			Han® PushPull protection cover, plastic, for RJ45, SCRJ, Power, Signal, device side, passive locking	Protection cover IP40	09 35 002 5401
				Protection cover IP65 / IP67 without fixing cord with plastic fixing cord with nylon fixing plastic cord	09 35 002 5403 XL 09 35 002 5402 09 35 002 5404
			Han® PushPull protection cover, plastic, for RJ45, SCRJ, Power, Signal, cable side	Protection cover IP40	09 35 002 5412
				Protection cover IP65 / IP67 without fixing cord with nylon fixing cord	09 35 002 5411 09 35 002 5413
			Han® PushPull cable to cable plastic housing	for outer cable diameter 6.5 ... 9.5 mm for outer cable diameter 9 ... 13 mm	09 35 002 0431 09 35 002 0433