

Number of contacts

4

1.5 A 50 V

Modu-
lar

Features

- Suitable for FOC and coaxial contacts acc. to D-Sub

Technical characteristics

| | |
|---|-------------------------------------|
| Number of contacts | 4 |
| Rated current | 1.5 A |
| Rated voltage | 50 V |
| Insulation resistance | $>10^{10} \Omega$ |
| Contact resistance | $\leq 10 \text{ m}\Omega$ |
| Impedance | 50 Ω , 75 Ω |
| Limiting temperature | -40 ... +125 °C |
| Mating cycles | ≥ 500 |
| Material (insert) | Polycarbonate (PC) |
| Colour (insert) | RAL 7032 (pebble grey) |
| Material (locking) | Copper alloy |
| Material (contacts) | Copper alloy, PBFE / PBTP / PI |
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant, compliant with exemption |

Specifications and approvals

EN 60664-1
IEC 61984
UL 1977 ECBT2.E235076
DNV GL

Details

ATTENTION when using coaxial contacts:

Male module 09 14 004 4501 with contacts 09 14 000 62xx or 09 69 28x 5xxx

Female module 09 14 004 4513 with contacts 09 14 000 61xx or 09 69 18x 5xxx

When removing the contacts, the two-piece module can be opened using a 7mm screwdriver. This destroys the module.

ATTENTION! Guide pins and bushes are prescribed (see chapter Han 80).