

## Features

- Contacts for fine stranded wire
- Low mating forces
- Suitable for HPR® hoods and housings
- UL approvals for axial-screw and screw termination

## Technical characteristics

Rated current	350 A
Rated voltage	2000 V
Rated impulse voltage	12 kV
Pollution degree	3
Insulation resistance	>10 <sup>10</sup> Ω
Contact resistance	≤0.3 mΩ, ≤0.2 mΩ
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500
Wire outer diameter	≤22 mm, ≤19.5 mm
Material (insert)	Polycarbonate (PC), Polyamide (PA)
Colour (insert)	RAL 7032 (pebble grey)
Material (contacts)	Copper alloy
Material flammability class acc. to UL 94	V-0
RoHS	compliant, compliant with exemption


## Derating

### Current carrying capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.

Measuring and testing techniques acc. to IEC 60512-5-2


Crimp termination



- ① Conductor cross-section 35 mm<sup>2</sup>
  - ② Conductor cross-section 50 mm<sup>2</sup>
  - ③ Conductor cross-section 70 mm<sup>2</sup>
  - ④ Conductor cross-section 95 mm<sup>2</sup>
  - ⑤ Conductor cross-section 120 mm<sup>2</sup>
- Three contacts in Han® 24 HPR

## Derating

Axial screw termination  
Screw termination



- ① Conductor cross-section 50 mm<sup>2</sup>
  - ② Conductor cross-section 70 mm<sup>2</sup>
  - ③ Conductor cross-section 95 mm<sup>2</sup>
  - ④ Conductor cross-section 120 mm<sup>2</sup>
- Three contacts in Han® 24 HPR

## Specifications and approvals

EN 60664-1  
IEC 61984  
DNV GL  
UL 1977 ECBT2.E235076

## Details

Electrical data up to 350 A 4000 V 18 kV 3 by using a hexagonal adapter and the HARTING cable gland, in order to realise the clearance and creepage distance.

Contact resistance crimp contact: ≤ 0.3 mOhm

Contact resistance screw contact: ≤ 0.2 mOhm

Contact resistance axial screw contact: ≤ 0.2 mOhm

### Remarks on the axial screw technique

The wire gauges mentioned in the catalogue refer to geometric wire gauges of cables.

Hex key (A/F 5) see chapter Han 90

For more technical details (i.e. number of crimping operations or crimping position) see eCatalogue

Crimping tools see chapter Han 90

### Remarks on the crimp technique

The wire gauges mentioned in the catalogue refer to geometric wire gauges of cables.