



Technical characteristics

Degree of protection acc. to IEC IP68
60529
Material (cable glands) Metal

Technical characteristics

RoHS compliant with exemption
RoHS exemptions **6c**: Copper alloy containing up to 4 % lead by weight

Identification	Size	Clamping range (mm)	Part number	Drawing (dimensions in mm)																																												
Cable gland, EMC version	M20	4 ... 6,5	19 62 000 5081	<table border="1"> <thead> <tr> <th>cable-Ø D</th> <th>SW</th> <th>E</th> <th>shield-Ø B</th> </tr> </thead> <tbody> <tr> <td>6.5 ... 9.5</td> <td>22</td> <td>24.4</td> <td>3,5 ... 8,5</td> </tr> <tr> <td>4 ... 6.5</td> <td>22</td> <td>24.4</td> <td>2,5 ... 6,5</td> </tr> <tr> <td>7 ... 10.5</td> <td>22</td> <td>24.4</td> <td>6,5 ... 10,5</td> </tr> <tr> <td>9 ... 13</td> <td>22</td> <td>24.4</td> <td>6,5 ... 10,5</td> </tr> <tr> <td>6.5 ... 9.5</td> <td>22</td> <td>31.2</td> <td>3 ... 8</td> </tr> <tr> <td>9 ... 13</td> <td>28</td> <td>31.2</td> <td>4,8 ... 8</td> </tr> <tr> <td>11.5 ... 15.5</td> <td>35</td> <td>38.5</td> <td>8 ... 13,5</td> </tr> <tr> <td>14 ... 18</td> <td>35</td> <td>38.5</td> <td>9 ... 14,5</td> </tr> <tr> <td>17 ... 20.5</td> <td>43</td> <td>47.3</td> <td>15 ... 20</td> </tr> <tr> <td>20 ... 25</td> <td>43</td> <td>47.3</td> <td>15 ... 20</td> </tr> </tbody> </table>	cable-Ø D	SW	E	shield-Ø B	6.5 ... 9.5	22	24.4	3,5 ... 8,5	4 ... 6.5	22	24.4	2,5 ... 6,5	7 ... 10.5	22	24.4	6,5 ... 10,5	9 ... 13	22	24.4	6,5 ... 10,5	6.5 ... 9.5	22	31.2	3 ... 8	9 ... 13	28	31.2	4,8 ... 8	11.5 ... 15.5	35	38.5	8 ... 13,5	14 ... 18	35	38.5	9 ... 14,5	17 ... 20.5	43	47.3	15 ... 20	20 ... 25	43	47.3	15 ... 20
	cable-Ø D	SW	E		shield-Ø B																																											
	6.5 ... 9.5	22	24.4		3,5 ... 8,5																																											
	4 ... 6.5	22	24.4		2,5 ... 6,5																																											
	7 ... 10.5	22	24.4		6,5 ... 10,5																																											
	9 ... 13	22	24.4		6,5 ... 10,5																																											
	6.5 ... 9.5	22	31.2		3 ... 8																																											
	9 ... 13	28	31.2		4,8 ... 8																																											
	11.5 ... 15.5	35	38.5		8 ... 13,5																																											
	14 ... 18	35	38.5		9 ... 14,5																																											
	17 ... 20.5	43	47.3		15 ... 20																																											
	20 ... 25	43	47.3		15 ... 20																																											
	M20	6,5 ... 9,5	19 62 000 5080																																													
M20	7 ... 10,5	19 62 000 5082																																														
M20	9 ... 13	19 62 000 5084																																														
M25	6,5 ... 9,5	19 62 000 5090																																														
M25	9 ... 13	19 62 000 5092																																														
M32	11,5 ... 15,5	19 62 000 5094																																														
M32	14 ... 18	19 62 000 5096																																														
M40	17 ... 20,5	19 62 000 5097																																														
M40	20 ... 25	19 62 000 5098																																														

