

## Features

- Suitable for Han E<sup>®</sup>, Han<sup>®</sup> EE / EEE, Han<sup>®</sup> Q and Han A<sup>®</sup> inserts
- Can be combined with standard crimp contacts in one connector if needed
- Iron and constantan contacts according to IEC 60584 type J
- According to EUROMAP 14, Part 1

## Technical characteristics

Contact resistance	≤1 mΩ
Material (contacts)	Iron, Constantan
RoHS	compliant

## Specifications and approvals





EN 60664-1  
IEC 61984

## Details

**Crimping tools** see chapter Han 90

### Remarks on the crimp technique

The wire gauges mentioned in the catalogue refer to geometric wire gauges of cables.

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)
		Male	Female	
Han E <sup>®</sup> , Crimp contact, Iron  Contact surface: Gold plated  	0.14 ... 0.37 0.5	09 33 000 6173 09 33 000 6172	09 33 000 6273 09 33 000 6272	 <p>Stripping length 7.5 mm</p>
Han E <sup>®</sup> , Crimp contact, Constantan  	0.14 ... 0.37 0.5	09 33 000 6163 09 33 000 6162	09 33 000 6263 09 33 000 6262	 <p>Stripping length 7.5 mm</p>