

## Features

- Standard Hoods/housings for industrial applications
- Slim, space saving construction type

## Technical characteristics

|                                                            |                                     |
|------------------------------------------------------------|-------------------------------------|
| Limiting temperature                                       | -40 ... +125 °C                     |
| Degree of protection acc. to IEC 60529                     | IP65                                |
| Type rating acc. to UL 50 / UL 50E                         | 4, 4X, 12                           |
| Material (hood/housing)                                    | Aluminium die-cast                  |
| Surface (hood/housing)                                     | Powder-coated                       |
| Colour (hood/housing)                                      | RAL 7037 (dust grey)                |
| Material (seal)                                            | NBR                                 |
| Material (locking)                                         | Polycarbonate (PC), Stainless steel |
| Colour (locking)                                           | RAL 7037 (dust grey)                |
| Material flammability class acc. to UL 94 (locking levers) | V-0                                 |
| RoHS                                                       | compliant, compliant with exemption |

## Specifications and approvals

UL 1977 ECBT2.E235076  
 CSA-C22.2 No. 182.3 ECBT8.E235076  
 DNV GL

CE

Housings