






Han E/  
EE

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)												
		Male	Female													
Han E®, Crimp contact, Relay contact, Contact surface: Silver plated 	0.75 ... 1 1.5 2.5	09 33 000 6109 09 33 000 6110 09 33 000 6111		 <table border="1"> <thead> <tr> <th>Conductor cross-section</th> <th>∅</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>0.75-1 mm<sup>2</sup> AWG 18</td> <td>1.45 mm</td> <td>7.5 mm</td> </tr> <tr> <td>1.5 mm<sup>2</sup> AWG 16</td> <td>1.75 mm</td> <td>7.5 mm</td> </tr> <tr> <td>2.5 mm<sup>2</sup> AWG 14</td> <td>2.25 mm</td> <td>7.5 mm</td> </tr> </tbody> </table>	Conductor cross-section	∅	Stripping length	0.75-1 mm <sup>2</sup> AWG 18	1.45 mm	7.5 mm	1.5 mm <sup>2</sup> AWG 16	1.75 mm	7.5 mm	2.5 mm <sup>2</sup> AWG 14	2.25 mm	7.5 mm
Conductor cross-section	∅	Stripping length														
0.75-1 mm <sup>2</sup> AWG 18	1.45 mm	7.5 mm														
1.5 mm <sup>2</sup> AWG 16	1.75 mm	7.5 mm														
2.5 mm <sup>2</sup> AWG 14	2.25 mm	7.5 mm														
FO contact, for 1 mm plastic fibre 		20 10 001 3311	20 10 001 3321	 <p>Crimp zone</p>												
Han E®, Han® EE, Han® EEE, Coding pin  <p>for crimp inserts only With loss of one contact</p>			09 33 000 9954	