


Number of contacts

4

4 A 32 V 0.8 kV 3
+ shielding



Modu-
lar

Technical characteristics





Number of contacts	4
Additional contacts	+ shielding
Rated current	4 A
Rated voltage	32 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Contact resistance, shielding	$\leq 100 \text{ m}\Omega$
Limiting temperature	-40 ... +85 °C
Mating cycles	≥ 500
Wire outer diameter	$\leq 2.3 \text{ mm}$
Transmission characteristics	Cat. 5, Class D up to 100 MHz

Technical characteristics

Material (insert)	Liquid crystal polymer (LCP), Polycarbonate (PC)
Material (shielding)	Copper alloy, nickel plated
Colour (insert)	RAL 7032 (pebble grey)
Material (contacts)	Copper alloy
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption

Specifications and approvals

EN 60664-1
IEC 61984

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)
		Male	Female	
Han-Modular®, Han® M12 module 		09 14 002 3061	09 14 002 3161	
Han-Modular®, D-coding, Crimp termination  Please order crimp contacts separately.	0.13 ... 0.82	09 14 881 1405	09 14 881 2405	 Cable diameter 5.7 ... 8.8 mm