


Identification	No. of contacts	Part number	Drawing	Dimensions in mm
----------------	-----------------	-------------	---------	------------------

Flat cable grey UL AWM-style 2651 CSA	9	09 18 009 700 <input type="checkbox"/>
	15	09 18 015 700 <input type="checkbox"/>
	25	09 18 025 700 <input type="checkbox"/>
	37	09 18 037 700 <input type="checkbox"/>



Conductor material _____ Copper tinned
 Gauge _____ AWG 28/7 0.089 mm²
 Voltage rating _____ 300 V_{r.m.s.}
 Current rating at 25 °C _____ 2.1 A max.
 Capacity unbalanced _____ 45.9 pF/m
 Impedance unbalanced _____ 105 Ω
 Propagation delay _____ 4.9 ns/m nominal
 Insulation material _____ PVC
 Temperature rating (operating) _____ -20 °C ... +105 °C
 Temperature rating (static) _____ -30 °C ... +105 °C
 Flammability rating _____ UL: VW-1
 Insulation resistance _____ > 100 MΩ/km

Length per reel

30.48 m
(100 feet)

1

100 m
(328 feet)

4