



## Unmanaged Plug-and-Play Ethernet Switches

for Assembly on DIN Rail in Control Cabinets

Commercial Temp.: 0 °C ... +55 °C / Industrial Temp.: -40 °C ... +70 °C

## Specification

Number of ports copper / termination	6 x 10BASE-Te / 100BASE-TX EEE / 1000BASE-T EEE RJ45 (twisted pair)
Number of ports F.O. / termination	1 x 100/1000 SFP
Nominal voltage	24 / 48 VDC =
Permissible voltage range	9 V ... 60 VDC =
Termination	Screw type terminal block, pluggable, 3-poles (+ / - / ⌀)
Current consumption typical @ 24 V / 48 V	178 mA / 92 mA
Dimensions (W x H x D)	25.0 x 142.0 x 107.5 mm (without pluggable screw type terminal block)
Weight	490 g
MTBF in million hours	0.89
Approvals	CE FCC CFR 47 Part 15, cUL US 508 listed, Det Norske Veritas (DNV), Germanischer Lloyd (GL), American Bureau of Shipping (ABS), Nippon Kaiji Kyokai (NK)

Identification	Part number	Drawing	Dimensions in mm
Ha-VIS eCon 3061GB-AC 0 °C ... +55 °C 1 x SFP	24 03 406 1310	<p>Technical drawing showing front and side views of the switch module. Dimensions are provided in millimeters: 14,2 (top height), 142,0 (total height), 8,2 (bottom height), 107,50 (width to terminal block), 109,75 (total width), 6,7 (width of terminal block), and 25,0 (depth).</p>	
Ha-VIS eCon 3061GBT-AC -40 °C ... +70 °C 1 x SFP	24 03 406 1300		