



Unmanaged Plug-and-Play Ethernet Switches

for Assembly on DIN Rail in Control Cabinets

Commercial Temp.: 0 °C ... +55 °C / Industrial Temp.: -40 °C ... +70 °C

Power Sourcing Equipment (PSE) with 4 Ports PoE+ (34.2 watts per port)

Specification

Number of ports copper / termination including PoE+ ports	6 x 10BASE-T _e / 100BASE-TX EEE / 1000BASE-T EEE RJ45 (twisted pair) 4 x PoE+ with 34.2 watts per port
Nominal voltage (without PoE / PoE / PoE+)	24 / 48 / 54 VDC =
Permissible voltage range	9 V ... 60 VDC =
Termination	Screw type terminal block, pluggable, 3-poles (+ / - / ⌀)
Current consumption typical @ 24 V / 48 V / 54 V	0.18 A / 1.44 A / 2.43 A
Dimensions (W x H x D)	25.0 x 142.0 x 107.5 mm (without pluggable screw type terminal block)
Weight	505 g
MTBF in million hours	1.01
Approvals	CE FCC CFR 47 Part 15, cUL US 508 listed, Det Norske Veritas (DNV), Germanischer Lloyd (GL), American Bureau of Shipping (ABS), Nippon Kaiji Kyokai (NK)

Identification	Part number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

Ha-VIS eCon 3060GB-A-P 0 °C ... +55 °C	24 03 406 0030	
Ha-VIS eCon 3060GBT-A-P -40 °C ... +70 °C	24 03 406 0020	