





Series	Han® 70 A Hybrid module	Han® 40 A Axial module	Han® 40 A Axial module	Han® 40 A Crimp module
Number of contacts	1 / 4	2	2	2
Termination	Axial screw terminal 	Axial screw terminal 	Axial screw terminal 	Crimp terminal 
Rated current	1 x 70 A / 4 x 16 A	40 A	40 A	40 A
Rated voltage	1000 V / 400 V	1000 V	1000 V	1000 V
Wire gauge	14 ... 22 mm <sup>2</sup> / 0.14 ... 4 mm <sup>2</sup>	2.5 ... 8 mm <sup>2</sup>	6 ... 10 mm <sup>2</sup>	1.5 ... 10 mm <sup>2</sup>
Male insert (M)	09 14 005 2647	09 14 002 2601	09 14 002 2602	09 14 002 3002
Female insert (F)	09 14 005 2742	09 14 002 2701	09 14 002 2702	09 14 002 3102
Series	Han® C Axial module	Han® C Axial module	Han® C module	Han® CC Protected module
Number of contacts	3	3	3	4
Termination	Axial screw terminal 	Axial screw terminal 	Crimp terminal 	Crimp terminal 
Rated current	40 A	40 A	40 A	40 A
Rated voltage	690 V	690 V	690 V	830 V
Wire gauge	2.5 ... 8 mm <sup>2</sup>	6 ... 10 mm <sup>2</sup>	1.5 ... 10 mm <sup>2</sup>	1.5 ... 6 mm <sup>2</sup>
Male insert (M)	09 14 003 2601	09 14 003 2602	09 14 003 3001	09 14 004 3041
Female insert (F)	09 14 003 2701	09 14 003 2702	09 14 003 3101	09 14 004 3141
Series	Han® CD module	Han E® module	Han® E Quick Lock module	Han® EE module
Number of contacts	3 / 4	6	6	8
Termination	Crimp terminal 	Crimp terminal 	Quick Lock termination 	Crimp terminal 
Rated current	40 A / 10 A	16 A	16 A	16 A
Rated voltage	830 V / 830 V	500 V	500 V	400 V
Wire gauge	1.5 ... 6 mm <sup>2</sup> / 0.14 ... 2.5 mm <sup>2</sup>	0.14 ... 4 mm <sup>2</sup>	0.5 ... 2.5 mm <sup>2</sup>	0.14 ... 4 mm <sup>2</sup>
Male insert (M)	09 14 007 3001	09 14 006 3001	09 14 006 2633	09 14 008 3001
Female insert (F)	09 14 007 3101	09 14 006 3101	09 14 006 2733	09 14 008 3101
Series	Han® EE Quick Lock module	Han® EE Quick Lock module	Han E® Protected module	Han® EEE module
Number of contacts	8	8	6	20
Termination	Quick Lock termination blauer Betätiger 	Quick Lock termination schwarzer Betätiger 	Crimp terminal 	Crimp terminal 
Rated current	16 A	16 A	16 A	16 A
Rated voltage	400 V	400 V	830 V	500 V
Wire gauge	0.5 ... 2.5 mm <sup>2</sup>	0.25 ... 1.5 mm <sup>2</sup>	0.14 ... 4 mm <sup>2</sup>	0.14 ... 4 mm <sup>2</sup>
Male insert (M)	09 14 008 2633	09 14 008 2634	09 14 006 3041	09 14 020 3001
Female insert (F)	09 14 008 2733	09 14 008 2734	09 14 006 3141	09 14 020 3101